

TECHSPEC® 12.0mm Dia. x 50mm FL, Uncoated, Plano-Convex Lens



Stock **#37-784** 3-4 DAYS
[Other Coating Options](#)

- 1 + **£24.65**

ADD TO CART

Qty 1-9
£24.65
Qty 10+
£22.10
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.00 +0.0/-0.025

Effective Focal Length EFL (mm):

50.00 @ 587.6nm
Back Focal Length BFL (mm): 48.75
Coating: Uncoated
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 1.90 ±0.05
Edge Thickness ET (mm): 1.19
Radius R ₁ (mm): 25.84
Clear Aperture CA (mm): 11
f/#: 4.17
Numerical Aperture NA: 0.12
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 350 - 2200

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View