


TECHSPEC[®] 12.7 x 12.7mm 1030nm 45°, Yb:YAG Laser Line Mirror



TECHSPEC[®] Yb:YAG Laser Line Mirrors

Stock #11-299 3-4 DAYS

⊖

1

⊕

£116.45

ADD TO CART

Qty 1-5
£116.45

Qty 6+
£104.55

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Quality:
10-5

Type:
Laser Mirror

Parallelism (arcmin):
<3

Clear Aperture (%): 85
Back Surface: Commercial Polish
Reflection at DWL (%): 99.8
Coating Specification: R_{abs} >99.8% @ 1030nm R_{avg} >99.5% @ 1020 - 1040nm
Wavelength Range (nm): 1020 - 1040
Surface Flatness (P-V): λ/10
Coating Type: Dielectric
Coating: Laser Mirror (1020-1040nm)
Design Wavelength DWL (nm): 1030
Dimensions (mm): 12.7 x 12.7 +0.00/-0.10
Thickness (mm): 6.35 ±0.20
Angle of Incidence (°): 45
Substrate: □ Fused Silica (Corning 7980)
Damage Threshold, By Design: □ 20 J/cm² @ 1030nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View