

TECHSPEC[®] 12.5mm Dia 0.63 NA, Uncoated, UV Fused Silica Aspheric Lens



TECHSPEC UV Fused Silica Aspheric Lenses



Stock **#87-975** ☒ In Stock

[Other Coating Options](#)



1



£318.75

ADD TO CART

Qty 1-5

£318.75

Qty 6+

£255.00

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.1

Effective Focal Length EFL (mm): 10.00 @ 587.6nm
Numerical Aperture NA: 0.63
Back Focal Length BFL (mm): 4.52
Substrate:  Fused Silica (Corning 7980)
Aspheric Design Wavelength (nm): 587.6
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: Uncoated
Centering (arcmin): ≤5
Surface Quality: 60-40
Clear Aperture CA (mm): 11
Edge Thickness ET (mm): 2.03
Center Thickness CT (mm): 8.00 ±0.1
f#: 0.79
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 200 - 2200
Conjugate Distance: Infinite
Power (diopters): 100.00

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View