

TECHSPEC® 12.5mm Dia x -25mm FL VIS 0° Coated, Negative Achromatic Lens



Stock **#62-486** 3-4 DAYS
[Other Coating Options](#)

- 1 + **£74.80**

ADD TO CART

Qty 1-5
£74.80
Qty 6+
£63.58
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.025

Effective Focal Length EFL (mm):

-25.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): -27.33
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 11.50
Centering (arcmin): <1
Center Thickness CT (mm): 4.55 ±0.10
Center Thickness CT 1 (mm): 2.00 ±0.05
Center Thickness CT 2 (mm): 2.55 ±0.05
Radius R₁ (mm): -17.75
Radius R₂ (mm): 12.17
Radius R₃ (mm): 109.75
Edge Thickness ET (mm): 5.74
Substrate:  N-BAF10 / N-SF10
Surface Quality: 40-20
f/#: 2.00
Numerical Aperture NA: 0.25
Coating: VIS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Negative Achromatic Lens
Wavelength Range (nm): 425 - 675

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View