

TECHSPEC® 12.5mm Dia x -75mm FL VIS 0° Coated, Negative Achromatic Lens



Stock **#62-489** ☐ In Stock
[Other Coating Options](#)

1 **£74.80**

ADD TO CART

Qty 1-5
£74.80
Qty 6+
£63.58
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.025

Effective Focal Length EFL (mm):

-75.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): -77.47
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 11.50
Centering (arcmin): <1
Center Thickness CT (mm): 5.50 ±0.10
Center Thickness CT 1 (mm): 2.50 ±0.05
Center Thickness CT 2 (mm): 3.00 ±0.05
Radius R ₁ (mm): -46.07
Radius R ₂ (mm): 36.65
Radius R ₃ (mm): 108.00
Edge Thickness ET (mm): 6.05
Substrate:  N-BK7 / N-SF5
Surface Quality: 40-20
f/#: 6.00
Numerical Aperture NA: 0.08
Coating: VIS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Negative Achromatic Lens
Wavelength Range (nm): 425 - 675

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View