

TECHSPEC® 12.7mm Dia., 1900 - 2200nm BBAR Coated, Ultrafast Thin Window



Stock #11-737

3-4 DAYS

-

1

+

£114.75

ADD TO CART

Qty 1-5

£114.75

Qty 6+

£103.27

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Abbe Number (v_d):
67.8

Bevel:
Protective as needed

Clear Aperture (%):
90

Diameter (mm): 12.70 +0.00/-0.10
Thickness (mm): 1.00 ±0.10
Coating: BBAR (1900-2200nm)
Coating Specification: R_{abs} <0.15% @ 1900 - 2200nm
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 0.52 (+5 to +35°C) 0.57 (0 to +200°C) 0.48 (-100 to +200°C)
Density (g/cm³): 2.20
Edges: Fine Ground
Index of Refraction n_d: 1.458
Knoop Hardness (kg/mm²): 522
Parallelism (arcsec): ≤30
Poisson's Ratio: 0.16
Substrate: Fused Silica IR Grade
Surface Quality: 20-10
Transmitted Wavefront, P-V: λ/6
Type: Ultrafast Window
Wavelength Range (nm): 1900 - 2200
Young's Modulus (GPa): 73

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View