

TECHSPEC[®] 12.7mm 45°, 2µm Laser Line Mirror



2µm Laser Line Mirrors

Stock **#37-501** CLEARANCE ☐ In Stock



1



£300.90

ADD TO CART

Qty 1-10

£300.90

Qty 11+

£266.05

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Quality:
40-20

Type:
Laser Mirror

Parallelism (arcmin):
<3

Clear Aperture (%) 90
Back Surface: Compensating Coating
Reflection at DWL (%) 99.6
Reflectivity (Rs%) 99.6
Reflectivity (Rp%) 99.9
Coating Specification: Rs >99.9% @ 1900 – 2200nm Rp >99.6% @ 1940 – 2100nm
Wavelength Range (nm): 1900 - 2200
Surface Flatness (P-V): λ/7 @ 2000nm
Coating Type: Dielectric
Coating: Laser Mirror (1900-2200nm)
Design Wavelength DWL (nm): 2000
Diameter (mm): 12.70 +0.0/-0.1
Thickness (mm): 6.35 ±0.2
Angle of Incidence (°): 45
Substrate: Fused Silica (Corning 7980)
Damage Threshold, By Design: >10 J/cm² @ 2000nm, 10ns, 10Hz

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant