

12.7mm 7°, 1030nm Highly-Dispersive Ultrafast Mirror

See More by [UltraFast Innovations \(UFI\)](#)



Stock #12-334 3-4 DAYS

- 1 + **£389.30**

ADD TO CART

Qty 1-3
£389.30
Qty 4+
£340.00
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Design Wavelength DWL (nm):
1030

Wavelength Range (nm):
1010 - 1070

Diameter (mm):
12.70 +0.0/-0.1

Angle of Incidence (°): 7
Reflection at DWL (%) : 99.9 (typical, s-polarization)
Thickness (mm): 6.35 ±0.2
Substrate: ☐ Fused Silica (Corning 7980)
Type: Laser Mirror
Coating Type: Dielectric
Coating Specification: R _{avg} >99.8%, GDD = -1000fs ² @ 1010 - 1070nm (s-polarization) R _{abs} >99.9% @ 1030nm (typical, s-polarization)
GDD Specification: -1000fs ² @ 1010 - 1070nm
Back Surface: Commercial Polish
Clear Aperture (%) : 80
Coating: Ultrafast (1010-1070nm)
Typical Applications: Yb:doped 1st Harmonic
Irregularity (P-V) @ 632.8nm: λ/10
Wedge (arcmin): 10 ±5
Minimum Reflectivity : >99.8% @ 1010 - 1070nm (s-polarization)
Damage Threshold, By Design: ☐ 0.3 J/cm ² @ 1030nm, 50fs, 1kHz, 100μm Beam Diameter

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant