

TECHSPEC® 12.7mm Dia. x 12.7mm FL, 8-12µm AR Coated, ZnSe Aspheric Lens

See More by [Coherent®](#)



TECHSPEC Zinc Selenide (ZnSe) Aspheric Lenses

Stock **#39-509** 3-4 DAYS

[Other Coating Options](#)



1



£688.50

ADD TO CART

Qty 1-10

£688.50

Qty 11+

£619.65

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.70 +0.00/-0.10

Effective Focal Length EFL (mm):
12.70

Numerical Aperture NA: 0.50
Back Focal Length BFL (mm): 11.25
Substrate:  Coherent® Infrared ZnSe
Asphere Figure Error, RMS @ 632.8nm: $\lambda/2$
Coating: BBAR (8000-12000nm)
Coating Specification: R _{avg} <0.5% @ 8 - 12μm
Centering (arcmin): ≤20
Centering, ETD (μm): ≤50.8
Surface Quality: 40-20
Clear Aperture CA (mm): 11.43
Edge Thickness ET (mm): 2.39
Center Thickness CT (mm): 3.50 ±0.10
f#: 1
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 8000 - 12000
Conjugate Distance: Infinite
Surface Roughness (Angstroms): <50 RMS
Power (P-V) @ 10.6μm: $\lambda/10$
Power (P-V) @ 632.8nm: $\lambda/10$

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View