

TECHSPEC® 12.7mm Dia x 75mm FL, NIR II Imaging Grade PCX Cylinder Lens



Stock **#34-628** ☒ In Stock

-

1

+

£80.75

ADD TO CART

Qty 1-5
£80.75
Qty 6+
£64.60
Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.70 +0.0/-0.025

Effective Focal Length EFL (mm):
75.00

Substrate: N-BK7
f#: 4.00
Numerical Aperture NA: 0.08
Coating: NIR II (750-1550nm)
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 750 - 1550
Back Focal Length BFL (mm): 73.68
Bevel: Protective bevel as needed
Center Thickness CT (mm): 2.00
Center Thickness Tolerance (mm): ±0.1
Clear Aperture CA (mm): 11.43
Coating Specification: R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm
Edge Thickness ET (mm): 1.48
Radius R₁ (mm): 38.76
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Plano Axis Wedge (arcmin): <5
Power Axis Wedge (arcmin): <5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant