

12.7mm Diameter x 15mm FL, MgF₂ Coated, PCX Condenser Lens



Stock #15-529

3-4 DAYS

[Other Coating Options](#)

-

1

+

£33.15

ADD TO CART

Qty 1-10

£33.15

Qty 11+

£29.75

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
12.70 +0.1/-0.3

Effective Focal Length EFL (mm):
15.00

Numerical Aperture NA:
0.42

Substrate: Float Glass
Focal Length Tolerance (%): ±7
Coating: MgF₂ (400-700nm)
Coating Specification: R_{avg} ≤ 1.75% @ 400 - 700nm
Centering (arcmin): ≤30
Surface Quality: 80-50 (typical)
Center Thickness CT (mm): 4.40 ±0.2
f/#: 1.18
Bevel: Protective bevel as needed
Radius R₂ (mm): Plano
Shape of Back Surface: Plano
Type: Condenser Lens
Wavelength Range (nm): 400 - 700
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant