

TECHSPEC® 12.7mm H x 12.7mm L x 25mm FL VIS 0°, Illumination Grade PCX Cylinder Lens



Stock **#36-209** 3-4 DAYS

- 1 + **£69.70**

ADD TO CART

Qty 1-5
£69.70

Qty 6+
£55.67

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Effective Focal Length EFL (mm):
25.00

Substrate: ☐
[N-BK7](#)

f/#:
1.96850393700787

Numerical Aperture NA: 0.25
Coating: VIS 0° (425-675nm)
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 425 - 675
Back Focal Length BFL (mm): 23.02
Center Thickness CT (mm): 3.00
Center Thickness Tolerance (mm): ±0.1
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 12.7 x 12.7
Edge Thickness ET (mm): 1.33
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 12.92
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant