

TECHSPEC[®] 12.7mm Silver and VIS 0° Coated, Mounted Corner Cube Retroreflector



Mounted N-BK7 Corner Cube Retroreflectors



Stock #12-216 3-4 DAYS

⊖ 1 ⊕

£310.25

ADD TO CART

Qty 1-5

£310.25

Qty 6+

£248.20

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Beam Deviation (arcsec):
±5

Coating:

MS 0° & Silver with protective overcoat
Diameter Tolerance (mm): +0.0/-0.1
Substrate: ☐ N-BK7
Inner Diameter (mm): 12.70
Outer Diameter (mm): 31.75
Surface Quality: 60-40
Mounting Threads: (2) ¼-20 Tapped Holes
Type: Retroreflector
Housing Tolerance (mm): Outer Diameter: +0/-0.5, Height:± 0.25
Image Orientation: Left-Handed
Coating Specification: Reflective Surfaces: R _{abs} > 97% FROM400 - 2500nm @ 0° AOI R _{avg} > 98% FROM400 - 2500nm @ 0° AOI Entrance: R _{avg} ≤0.4% @ 425 - 675nm
Ray Deviation (°): 180
Wavelength Range (nm): 425 - 675
Power (fringes) @ 632.8nm: 0.25
Irregularity (fringes) @ 632.8nm: 0.25

Regulatory Compliance

RoHS: Not Compliant
Certificate of Conformance: View