

12.7mm Dia. 1064nm $\lambda/2$ Quartz Waveplate Zero Order



Stock **#85-045** [CONTACT US](#)

-

1

+

£360.40

ADD TO CART

Qty 1+
£360.40

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
8.00

Coating:
Laser V-Coat (1064nm)

Design Wavelength DWL (nm):
1064

Diameter (mm):
12.70 +0.00/-0.25

Substrate: ☐
Crystal Quartz

Retardance: λ/2
Surface Quality: 10-5
Thickness (mm): 6.40 +0.00/-0.25
Type: Crystalline Waveplate
Construction: Crystalline
Transmitted Wavefront, P-V: λ/10 for central 80% of clear aperture
Parallelism (arcsec): <3
Retardance Tolerance: ±λ/200
Temperature Coefficient (λ/°C): 0.0001
Damage Threshold, By Design: ☐ 3.5 J/cm² @ 1064nm, 10ns
Retardance Order: 0

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View