

12.7mm Dia. 514.5nm λ /4 Quartz Waveplate Multiple Order



Stock **#85-075** 3-4 DAYS

- 1 + **£218.45**

ADD TO CART

Qty 1-5
£218.45

Qty 6+
£176.80

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
8.00

Coating:
Laser V-Coat (514.5nm)

Design Wavelength DWL (nm):
514.5

Diameter (mm):

12.70 +0.00/-0.25
Substrate: Crystal Quartz
Retardance: λ/4
Surface Quality: 10-5
Thickness (mm): 6.40 +0.00/-0.25
Type: Crystalline Waveplate
Construction: Crystalline
Transmitted Wavefront, P-V: λ/10 for central 80% of clear aperture
Parallelism (arcsec): <3
Retardance Tolerance: ±λ/200
Temperature Coefficient (λ/°C): 0.0015
Retardance Order: Multiple Order

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View