

TECHSPEC[®] 12.7mm Dia. x 44.5mm FL, VIS 0° Coated, Achromatic Lens



Stock **#49-776** ☐ In Stock

[Other Coating Options](#)

-

1

+

£68.85

ADD TO CART

Qty 1-5
£68.85
Qty 6+
£55.04
Volume Pricing
Request Quote

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.70 +0.0/-0.025

Effective Focal Length EFL (mm):

44.45
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 41.98
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 11.70
Centering (arcmin): <1
Center Thickness CT (mm): 5.00 ±0.20
Center Thickness CT 1 (mm): 3.00 ±0.10
Center Thickness CT 2 (mm): 2.00 ±0.10
Radius R ₁ (mm): 28.49
Radius R ₂ (mm): -20.03
Radius R ₃ (mm): -81.41
Edge Thickness ET (mm): 4.04
Substrate:  N-BAK1 / N-SF8
Surface Quality: 40-20
f/#: 3.5
Numerical Aperture NA: 0.14
Coating: VIS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 425 - 675

Regulatory Compliance

Reach 181: Compliant
RoHS 2015: Compliant
Certificate of Conformance: View