

TECHSPEC® 12mm Dia x 84mm FL UV-VIS Coated, UV Plano-Convex Lens



UV Fused Silica Plano-Convex (PCX) Lenses



Stock **#36-709** 3-4 DAYS

- 1 + **£112.63**

ADD TO CART

Qty 1-5

£112.63

Qty 6+

£90.10

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.00 +0.0/-0.025

Effective Focal Length EFL (mm):

84.00 @ 587.6nm
Back Focal Length BFL (mm): 82.28
Coating: UV-VIS (250-700nm)
Coating Specification: R _{abs} ≤1.0% @ 350 - 450nm R _{avg} ≤1.5% @ 250 - 700nm
Substrate: ☐ Fused Silica (Corning 7980)
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 2.50 ±0.05
Edge Thickness ET (mm): 2.03
Radius R₁ (mm): 38.51
Clear Aperture CA (mm): 11
f#: 7
Numerical Aperture NA: 0.07
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 250 - 700
Damage Threshold, Reference: ☐ 3 J/cm ² @ 355nm, 10ns 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant