

TECHSPEC® 12mm Dia. x 25mm FL 1550nm V-Coat, UV PCX Lens



Stock **#34-157** 3-4 DAYS

[Other Coating Options](#)



1



£119.85

ADD TO CART

Qty 1-5

£119.85

Qty 6+

£95.84

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.00 +0.0/-0.025

Effective Focal Length EFL (mm):

25.00 @ 587.6nm
Back Focal Length BFL (mm): 22.31
Coating: Laser V-Coat (1550nm)
Coating Specification: R _{abs} <0.25% @ 1550nm
Substrate: ☐ Fused Silica (Corning 7980)
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): ≤1
Center Thickness CT (mm): 3.92 ±0.05
Edge Thickness ET (mm): 2.22
Radius R₁ (mm): 11.46
Clear Aperture CA (mm): 11.00
f/#: 2.08
Numerical Aperture NA: 0.24
Design Wavelength DWL (nm): 587.6
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Edges: Fine Ground, Protective Bevel as Needed
Damage Threshold, By Design: ☐ 5 J/cm ² @ 1550nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant