

TECHSPEC[®] 12.7mm x -25mm FL, Uncoated Imaging Grade PCV Cylinder Lens



TECHSPEC[®] Beam Shaping PCV Cylinder Lenses

Stock #34-618 ☐ In Stock

-

1

+

£70.97

ADD TO CART

Qty 1-5
£70.97
Qty 6+
£56.95
Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.70 +0.0/-0.025

Effective Focal Length EFL (mm):
-25.00

Substrate: ☐
[N-BK7](#)

f/#: 2
Numerical Aperture NA: 0.25
Coating: Uncoated
Type: Cylinder Lens, Plano-Concave
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): -26.32
Bevel: Protective bevel as needed
Center Thickness CT (mm): 1.00
Center Thickness Tolerance (mm): ±0.1
Clear Aperture CA (mm): 11.43
Edge Thickness ET (mm): 2.56
Radius R₁ (mm): 12.92
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Plano Axis Wedge (arcmin): <5
Power Axis Wedge (arcmin): <5

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View