

LightPath 355230 | 1310nm Alignment, 0.55 NA Fiber Collimator w/ SMA Connector

See More by [Lightpath®](#)



Fiber Optic Collimator and Focuser Assemblies



Stock **#64-792** CLEARANCE 3-4 DAYS

- 1 + **£100.26**

ADD TO CART

Qty 1+

£100.26

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Effective Focal Length EFL (mm):
4.51 @ 780nm

Numerical Aperture NA:
0.55

Substrate: ☐
[D-ZLaF52LA](#)

Coating: BBAR (1050-1600nm)
Coating Specification: R _{abs} <1.0% @ 1050 - 1600nm
Surface Quality: 40-20
Clear Aperture CA (mm): 4.95
f#: 0.91
Bevel: Protective bevel as needed
Connector: SMA
Construction: 304L Stainless Steel Housing
Housing Diameter (mm): 11.00
Housing Length (mm): 9.6
Lightpath Lens Code: 355230
Mount: M11 x0.5
Type: Fiber Collimator
Wavelength Range (nm): 1050 - 1600
Conjugate Distance: Infinite
Lens Included: #87-155
Alignment Wavelength (nm): 1310

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant