

Ti:Sapphire Flat Top Beam Shaper 12mm | π Shaper 12_12_TiS_HP

See More by [AdlOptica](#)



Stock **#14-279** [CONTACT US](#)

-

1

+

£8,177.00

ADD TO CART

Qty 1-4

£8,177.00

Qty 5+

£7,358.45

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Design Wavelength DWL (nm):
800

Diameter (mm):
42.00

Entrance Beam Diameter, 1/e² (mm):
12.0 - 12.1

Model Number: πShaper 12_12_TiS_HP
Length (mm): 358.00
Mounting Threads: M27 x 1
Type: Beam Shaper
Weight (g): <530
Wavelength Range (nm): 700 - 900
Style: Flat Top
Damage Threshold, By Design: ☐ 3000 mJ/cm² @ 5ns (typical)
Output Diameter, FWHM (mm): 12.0

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant