

1550nm Flat Top Beam Shaper | π Shaper 6_6_1550

See More by [AdlOptica](#)



Flat Top Beam Shaper

Stock **#37-700** 3-4 DAYS

-

1

+

£5,235.15

ADD TO CART

Qty 1-4

£5,235.15

Qty 5+

£4,709.85

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Design Wavelength DWL (nm):

1550

Diameter (mm):

39.00

Entrance Beam Diameter, 1/e² (mm):

6.4-6.5

Model Number: πShaper 6_6_1550
Length (mm): 143.00
Mounting Threads: M27 x 1
Type: Beam Shaper
Weight (g): <270
Wavelength Range (nm): 1500 - 1600
Style: Flat Top
Damage Threshold, By Design: ☐ 20 mJ/cm ² @ 5ns (typical)
Output Diameter, FWHM (mm): 6.2

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant