

TECHSPEC® 15mm Dia., 2mm Thick, BBAR (1650-3000nm) AR Coated Sapphire Window



Stock **#15-993** 3-4 DAYS

- 1 + **£82.88**

ADD TO CART

Qty 1-24
£82.88
Qty 25+
£66.30
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Abbe Number (v_d):
72.24

Axis Orientation:
Random

Bevel:
Protective as needed

Birefringence (n_o-n_e): 0.008 for Visible Light Orthogonal to Optical Axis
Clear Aperture (%) : ≥90
Clear Aperture CA (mm) : 13.50
Diameter (mm) : 15.00 ±0.25
Thickness (mm) : 2.00 ±0.10
Coating : BBAR (1650-3000nm)
Coating Specification : R _{avg} <1% @ 1650 - 3000nm R _{abs} <2% @ 1650 - 3000nm
Coefficient of Thermal Expansion CTE (10⁻⁶/°C) : 8.8
Density (g/cm³) : 3.97
Edges : Fine Ground
Index of Refraction n_d : 1.77
Knoop Hardness (kg/mm²) : 1900
Parallelism (arcmin) : ≤3.5
Poisson's Ratio : 0.27
Substrate : Sapphire (Al ₂ O ₃)
Surface Flatness (P-V) : 2λ (typical)
Surface Quality : 80-50
Type : Protective Window
Wavelength Range (nm) : 1650 - 3000
Young's Modulus (GPa) : 435

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant