

1.8mm FL, No IR-Cut Filter, f/2, Micro Video Lens



Stock #36-182 3-4 DAYS

-

1

+

£50.15

ADD TO CART

Qty 1-49
£50.15
Qty 50+
£39.95
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length (mm):
15.70

Maximum Diameter (mm):
15.0

Maximum Image Circle (mm):
4.50

Horizontal Field of View @ Max Sensor Format:

122
Resolution, On-Axis: 160 lp/mm @ 20% Contrast
Resolution, 0.7 Field: 80 lp/mm @ 20% Contrast
Resolution, Full Field: 107 lp/mm @ 20% Contrast
Note: Standard
Type: M12 Imaging Lens
Focal Length FL (mm): 1.80
Maximum Sensor Format: 1/4"
Working Distance (mm): 400 - ∞
Mount: M12 x 0.5 (S-Mount)
Aperture (f/#): f/2
Distortion (%): -76.2
IR Cut Filter: No
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View