

TECHSPEC®

15mm Square Protected Silver Coated, λ/10 Mirror



15mm Square Protected Silver Coated, λ/10 Mirror, #68-326

Stock **#68-326** [CONTACT US](#)

-

1

+

£83.30

ADD TO CART

Qty 1-5

£83.30

Qty 6+

£66.72

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Flatness (P-V):
λ/10 (measured before coating)

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Back Surface:
Commercial Polish

Surface Quality: 20-10
Dimensions (mm): 15.0 x 15.0
Dimensional Tolerance (mm): +0.0/-0.20
Coating Specification: R_{avg} >98% @450 - 2000nm R_{avg} >98% @2000 - 10,000nm
Coating: Protected Silver (450-10000nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%): 90
Edges: Ground
Parallelism (arcsec): 30
Thickness (mm): 3.00 ±0.20
Type: Flat Mirror
Wavelength Range (µm): 0.45 - 10
Wavelength Range (nm): 450 - 10000
Length (mm): 15.00
Width (mm): 15.00
Damage Threshold, Reference: 0.5 J/cm² @532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant