

TECHSPEC[®] 15mm VIS-EXT, 50R/50T, Non-Polarizing Cube Beamsplitter



Stock #11-288 3-4 DAYS

-

1

+

£219.30

ADD TO CART

Qty 1-5
£219.30
Qty 6+
£171.70
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Beam Deviation (arcmin):
≤2

Bevel:
Protective bevel as needed

Clear Aperture (%):
>90

Coating: VIS-EXT (400-640nm)
Coating Specification: R_{avg} <0.5% @ 400 - 640nm
Construction: Cube
Dimensions (mm): 15.0 x 15.0 x 15.0 ±0.1
Reflection/Transmission Ratio (R/T): 50/50
Substrate: N-BK7
Surface Quality: 40-20
Type: Non-Polarizing Beamsplitter
Wavelength Range (nm): 400 - 640
[Ts-Tp]: <6%
Absolute Transmission (%): 45 ±10
Power (fringes) @ 632.8nm: 1.25
Irregularity (fringes) @ 632.8nm: 0.25

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View