

TECHSPEC[®] 19.1mm Dia. 1064nm, Nd:YAG Laser Line Beam Sampler



TECHSPEC[®] Nd:YAG Laser Line Beam Samplers

Stock #39-015 3-4 DAYS



1



£121.13

ADD TO CART

Qty 1-5

£121.13

Qty 6+

£109.22

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle of Incidence (°):
0 ±5

Clear Aperture (%):
90

Coating:
Laser V-Coat (1064nm)

Coating Specification: R_{abs} <0.25% @ 1064nm
Design Wavelength DWL (nm): 1064
Diameter (mm): 19.10 +0.00/-0.10
Index of Refraction n_d: 1.458
Parallelism (arcmin): <3
Substrate: Fused Silica (Corning 7980)
Surface Flatness (P-V): λ/10
Surface Quality: 10-5
Thickness (mm): 6.35 ±0.20
Type: Beam Sampler
Damage Threshold, By Design: 15 J/cm² @ 1064nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View