

TECHSPEC[®] 19.1mm Diameter Enhanced Aluminum Coated, λ/10 Mirror



Stock #39-203 3-4 DAYS

-

1

+

£74.80

ADD TO CART

Qty 1-5
£74.80
Qty 6+
£59.92
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
19.10 +0.00/-0.10

Surface Flatness (P-V):
λ/10 (measured before coating)

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Back Surface: Commercial Polish
Surface Quality: 20-10
Dimensional Tolerance (mm): +0.0/-0.10
Coating Specification: R _{avg} >95% @450 - 650nm
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%): 90
Edges: Ground
Parallelism (arcsec): <180
Thickness (mm): 6.35 ±0.20
Type: Flat Mirror
Wavelength Range (µm): 0.45 - 0.65
Wavelength Range (nm): 450 - 650
Damage Threshold, Reference: ☐ 0.2 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant