


## 203.2mm Dia. x 1mm High Efficiency Window



Stock **#63-218** 3-4 DAYS

- 1 + **£51.00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-5                       |
| £51.00                        |
| Qty 6+                        |
| £40.80                        |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):  
0

Bevel:  
Protective as needed

Clear Aperture (%):  
≥90

|                                                                       |
|-----------------------------------------------------------------------|
| <b>Clear Aperture CA (mm):</b><br>182.88                              |
| <b>Diameter (mm):</b><br>203.20 ±0.76                                 |
| <b>Thickness (mm):</b><br>1.00 ±0.25                                  |
| <b>Coating:</b><br>BBAR (425-700nm)                                   |
| <b>Coating Specification:</b><br>R <sub>avg</sub> ≤0.5% @ 425 - 700nm |
| <b>Edges:</b><br>Ground                                               |
| <b>Substrate:</b><br>Float Glass                                      |
| <b>Surface Quality:</b><br>80-50                                      |
| <b>Transmission (%):</b><br>96.9 Average (typical)                    |
| <b>Type:</b><br>Protective Window                                     |
| <b>Wavelength Range (nm):</b><br>425 - 700                            |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 233:</b><br><a href="#">Compliant</a>             |