


19.1mm Dia., 5 Arcsec, Bare Gold Replicated Hollow Metal Retroreflector



Replicated Hollow Metal Retroreflectors

Stock **#15-899** 3-4 DAYS

⊖ 1 ⊕ **£408.00**

ADD TO CART

Qty 1-9
£408.00
Qty 10+
£367.20
Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Beam Deviation (arcsec):
5

Clear Aperture CA (mm):
16.51

Coating:
Bare Gold

Diameter (mm): 19.10
Substrate: Aluminum
Height (mm): 26.17
Surface Quality: 60-40
Mounting Threads: 10-24
Type: Retroreflector
Dimensional Tolerance (mm): +0.025/-0.051
Image Orientation: Left-Handed
Coating Specification: R_{avg} >94% @ 700 - 800nm R_{avg} >97% @ 800 - 2000nm R_{avg} >98% @ 2 - 12μm
Ray Deviation (°): 180
Wavelength Range (nm): 700 - 12000
Style: Standard Profile

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View