

2050nm Flat Top Beam Shaper | π Shaper 6_6_2.05

See More by [AdlOptica](#)



Flat Top Beam Shaper

Stock #12-242 3-4 DAYS

-

1

+

£5,327.80

ADD TO CART

Qty 1-4
£5,327.80
Qty 5+
£4,793.15
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Design Wavelength DWL (nm):
2050

Diameter (mm):
39.00

Entrance Beam Diameter, 1/e² (mm):
6.4 - 6.5

Model Number: πShaper 6_6_2.05
Length (mm): 143.00
Mounting Threads: M27 x 1
Type: Beam Shaper
Weight (g): <270
Wavelength Range (nm): 1900 - 2160
Style: Flat Top
Damage Threshold, By Design: ☐ 50 mJ/cm ² @ 5ns (typical)
Output Diameter, FWHM (mm): 6.4

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant