

TECHSPEC[®] 20mm VIS, 70R/30T, Non-Polarizing Cube Beamsplitter



Stock #13-434 3-4 DAYS

-

1

+

£203.15

ADD TO CART

Qty 1-5
£203.15
Qty 6+
£160.65
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Beam Deviation (arcmin):
≤2

Bevel:
Protective bevel as needed

Clear Aperture (%):
>90

Coating: VS
Coating Specification: R _{avg} <0.5% @ 430 - 670nm
Construction: Cube
Dimensions (mm): 20.0 x 20.0 x 20.0 ±0.1
Reflection/Transmission Ratio (R/T): 70/30
Substrate: ☐ N-BK7
Surface Quality: 40-20
Type: Non-Polarizing Beamsplitter
Wavelength Range (nm): 430 - 670
[Ts-Tp]: <6%
Absolute Transmission (%): 25 ±10
Average Transmission (%): 25 ±5
Power (fringes) @ 632.8nm: 1.25
Irregularity (fringes) @ 632.8nm: 0.25

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View