


2400 Grooves/mm, 50mm Dia., 200nm Rowland Circle Concave Diffraction Grating

See More by [ZEISS](#)



ZEISS Concave Diffraction Gratings



Stock #11-539 3-4 DAYS



1



£522.75

ADD TO CART

Qty 1+

£522.75

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Groove Density (grooves/mm):
2400 ±3

Blaze Wavelength (nm):
200

Diameter (mm):

50.00
Coating: Bare Aluminum
Substrate: ☐ N-ZK7
Type: Rowland Circle
Diffraction Efficiency (%) : ≥40 @ 215nm ≥33 @ 275nm ≥28 @ 375nm
Radius of Curvature (mm): 398.83
Groove Profile: Sinusoidal
Angle of Incidence, α (°): -40
Diffraction Angle, β @ 200nm (°): 9.4
Diffraction Angle, β @ 300nm (°): -4.4
Object Distance, l_a @ 200nm: 305.5
Focal Distance, l_b @ 200nm: 393.5
Edge Thickness ET (mm): 9.3
Diffraction Area Diameter (mm): ≥44

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View