

TECHSPEC®

25/25.4mm Diameter Rotation Kinematic Mount, 3-Screws



25/25.4mm Diameter Rotation Kinematic Mount, 3-Screws, #36-636

Stock **#36-636** 3-4 DAYS



1



£153.00

ADD TO CART

Qty 1-4

£153.00

Qty 5+

£137.70

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Type:
Adjustable - Rotary & Tip-Tilt

Type of Optics:
Circular

Size of Compatible Optics (mm):
25.0 - 25.4

Number of Adjustment Screws: 3
Clear Aperture CA (mm): 22.0
Travel (mm): 9.0
Coarse Rotation (°): 360
Construction: Aluminum plates, stainless steel screws, and brass thread bushings
Angle Tolerance (°): 0.4 per 0.25mm turn
Fine Tilt Angle (°): ±5
Fine Tip Angle (°): ±5
Sensitivity per 1° Knob Rotation (arcsec): 4
Thermal Stability (μrad): <5
Adjustment Screw Pitch (mm): 0.25
Compatible Post: M4 x0.7, 8-32
Min. Thickness of Compatible Optics (mm): 1.8
Pointing Stability (μrad): 1.3

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant