

TECHSPEC® 25 x 25mm Protected Silver Coated, λ /10 ZERODUR® Mirror



Stock **#39-911** 3-4 DAYS

- 1 + **£109.65**

ADD TO CART

Qty 1-5
£109.65
Qty 6+
£87.55
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Flatness (P-V):
 λ /10 (measured before coating)

Substrate:

Back Surface:
Commercial Polish

Surface Quality: 20-10
Dimensions (mm): 25.0 x 25.0 +0.00/-0.20
Coating Specification: R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm
Coating: Protected Silver (450-10000nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%): 90
Edges: Ground
Parallelism (arcsec): 30
Thickness (mm): 4.00 ±0.20
Type: Flat Mirror
Wavelength Range (nm): 450 - 10000
Length (mm): 25.00
Width (mm): 25.00
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 0.1
Damage Threshold, Reference: ☐ 0.5 J/cm ² @ 532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant