

250mm Dia x 500mm Focal Length, PCX Condenser Lens



Stock **#67-200** 3-4 DAYS

-

1

+

£381.65

ADD TO CART

Qty 1-10
£381.65
Qty 11+
£336.60
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
250.00 +0.0/-0.5

Effective Focal Length EFL (mm):
500.00 @ 587.6nm

Back Focal Length BFL (mm):
476.6

Coating:

Uncoated
Substrate: N-BK7
Surface Quality: 120-80
Center Thickness CT (mm): 35.50
Edge Thickness ET (mm): 3.25
Radius R₁ (mm): 258.40
Clear Aperture CA (mm): 245
f/#: 2
Numerical Aperture NA: 0.25
Type: Condenser Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 350 - 2200

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View