


**TECHSPEC® 25.4 x 25.4mm 343nm 45°, Yb:YAG Laser Line Mirror**



TECHSPEC® Yb:YAG Laser Line Mirrors

Stock **#39-598** 3-4 DAYS

⊖ 1 ⊕ **£136.85**

ADD TO CART

Qty 1-5

£136.85

Qty 6+

£123.25

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Quality:  
10-5

Type:  
Laser Mirror

Parallelism (arcmin):  
<3

|                                                                                                                     |
|---------------------------------------------------------------------------------------------------------------------|
| <div>Clear Aperture (%):<br/>85</div>                                                                               |
| <div>Back Surface:<br/>Commercial Polish</div>                                                                      |
| <div>Reflection at DWL (%):<br/>99.8</div>                                                                          |
| <div>Coating Specification:<br/>R<sub>abs</sub> &gt;99.8% @ 343nm<br/>R<sub>avg</sub> &gt;99.5% @ 339 - 346nm</div> |
| <div>Wavelength Range (nm):<br/>339 - 346</div>                                                                     |
| <div>Surface Flatness (P-V):<br/>λ/10</div>                                                                         |
| <div>Coating Type:<br/>Dielectric</div>                                                                             |
| <div>Coating:<br/>Laser Mirror (339-346nm)</div>                                                                    |
| <div>Design Wavelength DWL (nm):<br/>343</div>                                                                      |
| <div>Dimensions (mm):<br/>25.4 x 25.4 +0.00/-0.10</div>                                                             |
| <div>Thickness (mm):<br/>6.35 ±0.20</div>                                                                           |
| <div>Angle of Incidence (°):<br/>45</div>                                                                           |
| <div>Substrate: <div>▢</div><a href="#">Fused Silica</a> (Corning 7980)</div>                                       |
| <div>Damage Threshold, Reference: <div>▢</div><br/>6 J/cm² @ 343nm, 20ns, 20Hz</div>                                |

### Regulatory Compliance

|                                                                 |
|-----------------------------------------------------------------|
| <div>RoHS 2015:<br/><a href="#">Compliant</a></div>             |
| <div>Reach 209:<br/><a href="#">Compliant</a></div>             |
| <div>Certificate of Conformance:<br/><a href="#">View</a></div> |