

TECHSPEC® 25.4 x 25.4mm x -50mm FL, NIR II Imaging Grade PCV Cylinder Lens



TECHSPEC® Beam Shaping PCV Cylinder Lenses

Stock **#35-018** 3-4 DAYS

⊖ 1 ⊕ **£98.60**

ADD TO CART

Qty 1-5
£98.60
Qty 6+
£78.63
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Effective Focal Length EFL (mm):
-50.00

Substrate: ☐
[N-BK7](#)

f/#:
2

Numerical Aperture NA: 0.25
Coating: NIR II (750-1550nm)
Type: Cylinder Lens, Plano-Concave
Wavelength Range (nm): 750 - 1550
Back Focal Length BFL (mm): -52.64
Bevel: Protective bevel as needed
Center Thickness CT (mm): 4.00
Center Thickness Tolerance (mm): ±0.1
Clear Aperture CA (mm): 22.86 x 22.86
Coating Specification: R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm
Dimensional Tolerance (mm): +0.0/-0.025
Dimensions (mm): 25.4 x 25.4
Edge Thickness ET (mm): 7.22
Radius R₁ (mm): 25.84
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Plano Axis Wedge (arcmin): <5
Power Axis Wedge (arcmin): <5
Axial Twist (arcmin): <3

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant