

TECHSPEC[®] 25.4 x 25.4mm EFL 90° Bare Gold 100Å Off-Axis Parabolic Mirror



Stock **#35-643** 3-4 DAYS

[Other Coating Options](#)

-

1

+

£204.00

ADD TO CART

Qty 1-5
£204.00
Qty 6+
£183.60
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Type:
Off-Axis Parabolic Mirror

Diameter (mm):
25.40 +0.00/-0.38

Effective Focal Length EFL (mm):

25.40
Focal Length Tolerance (%) : ±1
Radius of Curvature (mm) : 25.40
Coating : Bare Gold
Coating Type : Metal
Coating Specification : R _{avg} ≥94% @ 700 - 800nm R _{avg} ≥97% @ 800 - 2,000nm R _{avg} ≥98% @ 2,000 - 12,000nm
Off-Set Angle (°) : 90
Parent Focal Length PFL (mm) : 12.7
Surface Figure, RMS : λ/4
Surface Roughness (Angstroms) : <100 RMS
Wavelength Range (nm) : 700 - 12000
Clear Aperture (%) : 90
Surface Quality : 80-50
Compatible Mounting Plates : #47-111
Substrate : Aluminum 6061-T6
Y Offset (mm) : 25.4
Reflected Wavefront, RMS : λ/2

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 235 : Compliant