

TECHSPEC[®] 25.4 x 272.2mm EFL 30° Protected Gold 100Å Off-Axis Parabolic Mirror



TECHSPEC Gold Off-Axis Parabolic Mirrors

Stock #35-617 3-4 DAYS

[Other Coating Options](#)

-

1

+

£565.25

ADD TO CART

Qty 1-5

£565.25

Qty 6+

£508.72

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Type:
Off-Axis Parabolic Mirror

Diameter (mm):
25.40 +0.00/-0.38

Effective Focal Length EFL (mm): 272.24
Focal Length Tolerance (%): ±1
Radius of Curvature (mm): 508.00
Coating: Protected Gold (700-10000nm)
Coating Type: Metal
Coating Specification: R_{avg} ≥94% @ 700 - 800nm R_{avg} ≥97% @ 800 - 2,000nm R_{avg} ≥98% @ 2,000 - 12,000nm
Off-Set Angle (°): 30
Parent Focal Length PFL (mm): 254.00
Surface Figure, RMS: λ/4
Surface Roughness (Angstroms): <100 RMS
Wavelength Range (nm): 700 - 10000
Clear Aperture (%): 90
Surface Quality: 80-50
Compatible Mounting Plates: #47-111
Substrate: Aluminum 6061-T6
Y Offset (mm): 136.12
Reflected Wavefront, RMS: λ/2

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant