

TECHSPEC[®] 25.4 x 50.8mm EFL 60° Protected Aluminum 100Å Off-Axis Parabolic Mirror



TECHSPEC Aluminum Off-Axis Parabolic Mirrors

Stock **#35-498** 3-4 DAYS

[Other Coating Options](#)



1



£157.25

ADD TO CART

Qty 1-5

£157.25

Qty 6+

£141.53

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Type:
Off-Axis Parabolic Mirror

Diameter (mm):
25.40 +0.00/-0.38

Effective Focal Length EFL (mm):

50.80
Focal Length Tolerance (%): ±1
Radius of Curvature (mm): 76.20
Coating: Protected Aluminum (400-2000nm)
Coating Type: Metal
Coating Specification: R _{avg} ≥85% @ 400 - 700nm R _{avg} ≥97% @ 2,000 - 12,000nm
Off-Set Angle (°): 60
Parent Focal Length PFL (mm): 38.1
Surface Figure, RMS: λ/4
Surface Roughness (Angstroms): <100 RMS
Wavelength Range (nm): 400 - 2000
Clear Aperture (%): 90
Surface Quality: 80-50
Compatible Mounting Plates: #47-111
Substrate: Aluminum 6061-T6
Y Offset (mm): 43.99
Reflected Wavefront, RMS: λ/2

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant