


TECHSPEC® 25.4 x 25.4mm 1030nm 0-45°, Yb:YAG Laser Line Mirror



TECHSPEC® Yb:YAG Laser Line Mirrors

Stock #11-313 3-4 DAYS

⊖ 1 ⊕ **£146.20**

ADD TO CART

Qty 1-5

£146.20

Qty 6+

£131.75

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Quality:
10-5

Type:
Laser Mirror

Parallelism (arcmin):

<3

Clear Aperture (%):
85

Back Surface:
Commercial Polish

Reflection at DWL (%):
99.8

Coating Specification:
R_{abs} >99.8% @ 1030nm

Wavelength Range (nm):
1020 - 1040

Surface Flatness (P-V):
λ/10

Coating Type:
Dielectric

Coating:
Laser Mirror (1030nm)

Design Wavelength DWL (nm):
1030

Dimensions (mm):
25.4 x 25.4 +0.00/-0.10

Thickness (mm):
6.35 ±0.20

Angle of Incidence (°):
0-45

Substrate:
[Fused Silica](#) (Coming 7980)

Damage Threshold, By Design:
15 J/cm² @ 1030nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Reach 209:
[Compliant](#)

Certificate of Conformance:
[View](#)
