

25.4mm Dia. 1064nm λ /4 Quartz Waveplate Zero Order



Stock #14-289

3-4 DAYS

-

1

+

£414.80

ADD TO CART

Qty 1-5
£414.80
Qty 6+
£335.75
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
20.00

Coating:
Laser V-Coat (1064nm)

Design Wavelength DWL (nm):
1064

Diameter (mm):

25.40 +0.00/-0.25
Substrate: Crystal Quartz
Retardance: $\lambda/4$
Surface Quality: 10-5
Thickness (mm): 6.00 +0.00/-0.25
Type: Crystalline Waveplate
Construction: Crystalline
Transmitted Wavefront, P-V: $\lambda/10$
Parallelism (arcsec): <3
Retardance Tolerance: $\pm\lambda/300$
Temperature Coefficient ($\lambda/^\circ\text{C}$): 0.0001
Coating Specification: $R_{\text{abs}} < 0.2\%$ @ 1064nm
Retardance Order: 0
Configuration: Air Spaced

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant