

TECHSPEC® 25.4mm Dia. x 200mm EFL, Uncoated, Concave Laser Mirror



TECHSPEC Uncoated Concave Mirrors

Stock **#39-978** 3-4 DAYS

⊖ 1 ⊕ **£91.80**

ADD TO CART

Qty 1-5
£91.80
Qty 6+
£81.60
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Substrate: ☐
[Fused Silica](#) (Coming 7980)

Surface Quality:
20-10

Diameter (mm):
25.40 +0.00/-0.20

Effective Focal Length EFL (mm): 200.00
Radius of Curvature (mm): 400.00
Coating: Uncoated
Back Surface: Fine Grind
Center Thickness CT (mm): 6.15
Clear Aperture (%): 90
Edge Thickness ET (mm): 6.35 ±0.10
Radius R ₁ (mm): 400.00
Type: Concave Mirror
Irregularity (P-V) @ 632.8nm: λ/10

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View