

TECHSPEC® 25.4mm Dia. x 35mm FL, 266nm Coated, Laser Grade PCX Lens



TECHSPEC Laser Grade PCX Lenses

Stock **#38-646** 3-4 DAYS

[Other Coating Options](#)



1



£172.55

ADD TO CART

Qty 1-5

£172.55

Qty 6+

£137.70

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.40 +0.00/-0.025

Effective Focal Length EFL (mm):
35.00 @355nm

Back Focal Length BFL (mm):

28.55
Coating: Laser V-Coat (266nm)
Coating Specification: R _{abs} <0.25% @ 266nm
Substrate: ☐ Fused Silica (Corning 7980)
Surface Quality: 10-5
Power (P-V) @ 632.8nm: λ
Irregularity (P-V) @ 632.8nm: λ/10
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 9.53 ±0.10
Edge Thickness ET (mm): 3.04
Radius R₁ (mm): 16.66
Clear Aperture CA (mm): 21.59
f/#: 1.38
Numerical Aperture NA: 0.36
Design Wavelength DWL (nm): 266
Type: Plano-Convex Lens
Bevel: Protective Bevel As Needed
Damage Threshold, By Design: ☐ 3 J/cm ² @ 266nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View