

TECHSPEC®

25.4mm Dia. x 5mm Thickness, Uncoated, ZnSe Window



Stock #39-398

3-4 DAYS

-

1

+

£259.25

ADD TO CART

Qty 1-10
£259.25
Qty 11+
£233.32
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Bevel:

Protective as needed

Clear Aperture (%):

90

Clear Aperture CA (mm):

22.86

Diameter (mm): 25.40 +0.0/-0.1
Thickness (mm): 5.00 ±0.1
Coating: Uncoated
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 7.57
Density (g/cm³): 5.27
Edges: Fine Ground
Index of Refraction n_d: 2.631
Knoop Hardness (kg/mm²): 120
Parallelism (arcmin): <3
Poisson's Ratio: 0.28
Substrate: Zinc Selenide (ZnSe)
Surface Flatness (P-V): λ/10 @ 10.6μm
Surface Quality: 40-20
Type: Protective Window
Wavelength Range (nm): 600 - 18000

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View