

TECHSPEC[®] 25.4mm Diameter x 1000mm FL, Uncoated, Ultrafast Thin PCX Lens



Stock #11-727 3-4 DAYS

[Other Coating Options](#)

-

1

+

£89.25

ADD TO CART

Qty 1-5

£89.25

Qty 6+

£79.05

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.40 +0.00/-0.10

Effective Focal Length EFL (mm):
1,001.17 @587.6nm

Back Focal Length BFL (mm):

1000.07
Coating: Uncoated
Substrate: ☐ Fused Silica (Corning 7980)
Surface Quality: 20-10
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/8
Focal Length Tolerance (%): ±1
Centering (arcmin): <3
Center Thickness CT (mm): 1.60 ±0.10
Edge Thickness ET (mm): 1.43
Radius R₁ (mm): 459.00
Clear Aperture CA (mm): 22.86
f/#: 39.38
Numerical Aperture NA: 0.013
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 200 - 2200

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View