


TECHSPEC[®] 25.4mm Diameter x 300mm FL, 700-900nm Coated, Ultrafast Thin PCX Lens



Stock #11-662 3-4 DAYS

[Other Coating Options](#)

-

1

+

£112.20

ADD TO CART

Qty 1-5
£112.20
Qty 6+
£98.60
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.40 +0.00/-0.10

Effective Focal Length EFL (mm):
300.35 @587.6nm

Back Focal Length BFL (mm):

299.25
Coating: BBAR (700-900nm)
Coating Specification: R _{abs} <0.2% @ 700 - 900nm
Substrate: ☐ Fused Silica (Corning 7980)
Surface Quality: 20-10
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/8
Focal Length Tolerance (%): ±1
Centering (arcmin): <3
Center Thickness CT (mm): 1.60 ±0.10
Edge Thickness ET (mm): 1.01
Radius R₁ (mm): 137.70
Clear Aperture CA (mm): 22.86
f/#: 11.82
Numerical Aperture NA: 0.043
Design Wavelength DWL (nm): 800
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 700 - 900
Angle of Incidence (°): 0
Damage Threshold, By Design: ☐ 10 J/cm ² @ 532nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View