


TECHSPEC[®] 25.4mm Diameter x 200mm FL, Uncoated, IR Ultrafast Thin PCX Lens



Stock #11-700 3-4 DAYS

[Other Coating Options](#)

-

1

+

£117.30

ADD TO CART

Qty 1-5
£117.30

Qty 6+
£102.85

Volume Pricing
Request Quote

ⓘ

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.40 +0.00/-0.10

Effective Focal Length EFL (mm):
200.23 @587.6nm

Back Focal Length BFL (mm):

199.14
Coating: Uncoated
Substrate: ☐ Fused Silica IR Grade
Surface Quality: 20-10
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/8
Focal Length Tolerance (%): ±1
Centering (arcmin): <3
Center Thickness CT (mm): 1.60 ±0.10
Edge Thickness ET (mm): 0.72
Radius R₁ (mm): 91.80
Clear Aperture CA (mm): 22.86
f/#: 7.88
Numerical Aperture NA: 0.064
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 200 - 3500

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View