

TECHSPEC® 25.4mm Silver and VIS 0° Coated, Mounted Corner Cube Retroreflector



Mounted N-BK7 Corner Cube Retroreflectors



Stock **#12-217** 3-4 DAYS

⊖ 1 ⊕

£335.75

ADD TO CART

Qty 1-5
£335.75
Qty 6+
£268.60
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Beam Deviation (arcsec):
±3

Coating:

MS 0° & Silver with protective overcoat

Diameter Tolerance (mm):
+0.0/-0.1

Substrate: ☐
N-BK7

Inner Diameter (mm):
25.40

Outer Diameter (mm):
38.10

Surface Quality:
60-40

Mounting Threads:
(2) ¼-20 Tapped Holes

Type:
Retroreflector

Housing Tolerance (mm):
Outer Diameter: +0/-0.5, Height: ±0.25

Image Orientation:
Left-Handed

Coating Specification:
Reflective Surfaces: R_{abs} > 97% FROM400 - 2500nm
@ 0° AOI
R_{avg} > 98% FROM400 - 2500nm @ 0° AOI
Entrance: R_{avg} ≤0.4% @ 425 - 675nm

Ray Deviation (°):
180

Wavelength Range (nm):
425 - 675

Power (fringes) @ 632.8nm:
0.25

Irregularity (fringes) @ 632.8nm:
0.25

Regulatory Compliance

RoHS 2015:
Not Compliant

Certificate of Conformance:
[View](#)